

Model 6821-0 (49ST/Canada)  
UPC: 696471068214

1 of 2



## FEATURES

- EASY PRIME™ Funnel design for quick and easy priming
- Hose kit included - 10' suction hose, 25' of discharge hose strainers and connectors
- Powerful Generac Pump - Can pump up to 80 gallons per minute
- Color coded suction and discharge ports to ensure the correct hose connections
- Durable design - Carbon Ceramic Seal, Cast Iron Volute and Impeller
- Generac's 79cc OHV engine with splash lubrication provides a long engine life

## Specifications

Engine Type	4 cycle/OHV
Engine Displacement (cc)	79.8
Start Type	Recoil Pull Start
Low Oil Shutdown Method	N/A
Recommended Oil	10W-30 / SAE30
Fuel Capacity (gal.) L	(0.4) 1.5
Max Run Time	1.5hrs
Flow (GPM) LPM	(80) 303
Max Total Head (ft.) m	(80) 24.4
Max Suction Lift (ft.) m	(26) 7.9
Mechanical Seal Type	Carbon Ceramic
Solid Handling (in.)	N/A
Suction Port (NPT)	1.5
Discharge Port (NPT)	1.5
Pump Housing	Aluminum
Impeller	Cast Iron
Volute	Cast Iron
Hose Kit Included	Yes
Discharge Hose Length (ft.) m	(25) 7.6
Suction Hose Length (ft.) m	(10) 3
Hose Connections	Plastic Speed Nut
Strainer	Plastic
Wheel Kit	N/A
Country of Origin	China
Warranty	1 Year

Manual Part #	OK9077
Length (in) mm	(16.8) 426
Width (in) mm	(13.1) 332
Height (in) mm	(17.4) 442
Unit Weight (lbs) kg	(38.6) 16.7
Carton Length (in) mm	(21.1) 535
Carton Width(in) mm	(18.7) 475
Carton Height (in) mm	(18.2) 462
Shipping Weight (lbs) kg	(53.0) 24.0

