

Power Inlet Boxes

Commercial/Residential
For Portable Generators



Models 6342, 6343, 6344




Models 6345, 6346, 6347



Models 6336, 6339, 6337,
6340, 6338, 6341

Features

- Safely connects your portable generator to your transfer switch.





Power Inlet Boxes

Specifications

| Model | 6342 | 6336 | 6339 | 6345 | 6343 | 6337 | 6340 | 6346 |
|--|---|---|------------------------------------|---|---|---|------------------------------------|---|
| UPC | 696471063424 | 696471063363 | 696471063394 | 696471063455 | 696471063431 | 696471063370 | 696471063400 | 696471063462 |
| NEMA Configuration | L14-20 | L14-20 | L14-20 with spring loaded flip lid | | L14-30 | L14-30 | L14-30 with spring loaded flip lid | |
| Amperage | 20 | | | | 30 | | | |
| Voltage Rating | 125/250 VAC | | | | 125/250 VAC | | | |
| Maximum Generator Size (Watts) | 5000 | | | | 7500 | | | |
| Enclosure Material | Corrosion-resistant aluminum provides long life, and can be painted. Retains raintight rating while in use. | Non-metallic resin enclosure includes 6 knockouts for ultimate wiring flexibility. Made from durable, high-impact, glass-filled nylon. Retains raintight rating while in use. | | Corrosion-resistant aluminum provides long life, and can be painted. Flip Lid covers the inlet to keep out nesting insects, dirt, moisture, and more. | Corrosion-resistant aluminum provides long life, and can be painted. Retains raintight rating while in use. | Non-metallic resin enclosure includes 6 knockouts for ultimate wiring flexibility. Made from durable, high-impact, glass-filled nylon. Retains raintight rating while in use. | | Corrosion-resistant aluminum provides long life, and can be painted. Flip Lid covers the inlet to keep out nesting insects, dirt, moisture, and more. |
| Raintight Enclosure | • | • | • | • | • | • | • | • |
| Compatible Generac Generators | GP3250, LP3250, XG4000, XP4000 | | | | GP3250, LP3250, XG4000, XP4000, GP5500, GP6500E, GP7500E, XG6500, XG7000E, XG8000E, XP6500E, XP8000E | | | |
| Compatible Transfer Switches (Model #'s) | 6376, 6377, 6378, 6379 | | | | 6376, 6378, 6377, 6379, 6382 | | | |
| Warranty | 2 Year | | | | | | | |

| Model | 6344 | 6338 | 6341 | 6347 |
|--|---|---|------------------------------------|---|
| UPC | 696471063448 | 696471063387 | 696471063417 | 696471063479 |
| NEMA Configuration | CS6365 | CS6365 | CS6365 with spring loaded flip lid | |
| Amperage | 50 | | | |
| Voltage Rating | 125/250 VAC | | | |
| Maximum Generator Size (Watts) | 12500 | | | |
| Enclosure Material | Corrosion-resistant aluminum provides long life, and can be painted. Retains raintight rating while in use. | Non-metallic resin enclosure includes 6 knockouts for ultimate wiring flexibility. Made from durable, high-impact, glass-filled nylon. Retains raintight rating while in use. | | Corrosion-resistant aluminum provides long life, and can be painted. Flip Lid covers the inlet to keep out nesting insects, dirt, moisture, and more. |
| Raintight Enclosure | • | • | • | • |
| Compatible Generac Generators | GP15000E, GP17500E, XG10000E, XP10000E | | | |
| Compatible Transfer Switches (Model #'s) | 6380, 6381, 6335 | | | |
| Warranty | 2 Year | | | |

| Spring Loaded Flip Lid - Model 6393 | |
|-------------------------------------|--|
| Accessory |  <p>Compatible with any Generac GenTran Power Inlet Box models 6342, 6343, 6344, 6336, 6337, & 6338 Must be mounted prior to installation UL Listed</p>  |

Dimensions and Weights

| Model | 6342 | 6336 | 6339 | 6345 | 6343 | 6337 | 6340 | 6346 | 6344 | 6338 | 6341 | 6347 | 6393 |
|---------------------------------|--------------------------|----------------|---------------------|------------------------|--------------------------|----------------|---------------------|------------------------|--------------------------|----------------|------------------------|---------------------|-------------------|
| Product L x W x H in (mm) | 6x5x5 (152x127x127) | | 5x5x7 (127x127x178) | | 6x5x5 (152x127x127) | | 5x5x7 (127x127x178) | | 6x5x5 (152x127x127) | | 5x5x7 (127x127x178) | | 6 x 8 (152 x 203) |
| Product Weight lb (kg) | 3 (1.25) | 2 (1) | 3 (1.25) | 3 (1.25) | 3 (1.25) | 2 (1) | 3 (1.25) | 3 (1.25) | 3 (1.25) | 2 (1) | 3 (1.25) | 3 (1.25) | 0.5 (0.2) |
| Master Carton Quantity | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 5 |
| Master Carton UPC | 20696471063428 | 20696471063367 | 20696471063398 | 20696471063459 | 20696471063435 | 20696471063374 | 20696471063404 | 20696471063466 | 20696471063442 | 20696471063381 | 20696471063411 | 20696471063473 | 20696471063930 |
| Master Carton L x W x H in (mm) | 16.5x6.5x6 (419x165x152) | | | 16.5x5x7 (419x127x178) | 16.5x6.5x6 (419x165x152) | | | 16.5x5x7 (419x127x178) | 16.5x6.5x6 (419x165x152) | | 16.5x5x7 (419x127x178) | 9x6x5 (229x152x127) | |
| Master Carton Weight lb (kg) | 9 (4) | 6 (3) | 9 (4) | 9 (4) | 9 (4) | 6 (3) | 9 (4) | 9 (4) | 9 (4) | 6 (3) | 9 (4) | 9 (4) | 3 (1.25) |



Generac Power Systems, Inc. • P.O. Box 8, Waukesha, WI 53187 • generac.com